

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839629

Luminaire Tested: **LDS4C08D010 EU4089040 4LBPSMMS**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839629  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C08D010 EU4089040 4LBPSMMS  
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 4LBPS TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 717.1 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839629

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBPSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P839629

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBPSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46254
5°	46098
10°	45583
15°	44808
20°	43797
25°	42632
30°	41281
35°	39699
40°	37688
45°	34279
50°	28287
55°	20841
60°	14128
65°	8285
70°	3269
75°	759
80°	990
85°	1692



TEST NUMBER: P839629

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBPSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.4	4.9
10°-20°	99.2	13.8
20°-30°	144.7	20.2
30°-40°	165.1	23.0
40°-50°	150.1	20.9
50°-60°	88.5	12.3
60°-70°	29.7	4.1
70°-80°	3.1	0.4
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.3	38.9
0°-40°	444.4	62.0
0°-60°	683.1	95.3
0°-90°	717.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	376	
5°	374	35
15°	352	99
25°	314	145
35°	265	165
45°	197	150
55°	97	89
65°	28	30
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839629

CATALOG NUMBER: LDS4C08D010 EU4089040 4LBPSMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	376.5
2.5°	375.9
5°	373.8
7.5°	370.3
10°	365.4
12.5°	359.2
15°	352.3
17.5°	344.1
20°	335.0
22.5°	325.1
25°	314.5
27.5°	302.9
30°	291.0
32.5°	278.1
35°	264.7
37.5°	250.1
40°	235.0
42.5°	217.4
45°	197.3
47.5°	174.0
50°	148.0
52.5°	122.1
55°	97.3
57.5°	76.1
60°	57.5
62.5°	41.7
65°	28.5
67.5°	17.4
70°	9.1
72.5°	3.5
75°	1.6
77.5°	1.6
80°	1.4
82.5°	1.2
85°	1.2
87.5°	1.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)