

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839219

Luminaire Tested: **LD4C15D010 EU4159050 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P839219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15D010 EU4159050 4LBSH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1572.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839219

CATALOG NUMBER: LD4C15D010 EU4159050 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839219

CATALOG NUMBER: LD4C15D010 EU4159050 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100998
5°	100533
10°	98464
15°	94882
20°	90510
25°	85629
30°	80774
35°	76053
40°	71607
45°	66751
50°	60874
55°	53761
60°	45505
65°	35727
70°	25503
75°	13955
80°	2476
85°	0



TEST NUMBER: P839219

CATALOG NUMBER: LD4C15D010 EU4159050 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	4.9
10°-20°	209.3	13.3
20°-30°	290.7	18.5
30°-40°	317.2	20.2
40°-50°	295.9	18.8
50°-60°	224.6	14.3
60°-70°	123.0	7.8
70°-80°	33.8	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.0	36.7
0°-40°	894.2	56.9
0°-60°	1414.7	90.0
0°-90°	1572.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1572.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	822	
5°	815	77
15°	746	209
25°	632	291
35°	507	317
45°	384	296
55°	251	225
65°	123	123
75°	29	34
85°	0	0
90°	0	



TEST NUMBER: P839219

CATALOG NUMBER: LD4C15D010 EU4159050 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	822.1
2.5°	822.1
5°	815.2
7.5°	804.9
10°	789.3
12.5°	768.5
15°	746.0
17.5°	718.3
20°	692.3
22.5°	661.2
25°	631.7
27.5°	602.4
30°	569.4
32.5°	538.3
35°	507.1
37.5°	476.0
40°	446.5
42.5°	415.4
45°	384.2
47.5°	353.1
50°	318.5
52.5°	285.6
55°	251.0
57.5°	218.1
60°	185.2
62.5°	152.3
65°	122.9
67.5°	95.2
70°	71.0
72.5°	48.5
75°	29.4
77.5°	13.8
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)