

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839235

Luminaire Tested: **LD4C20D010 EU4209050 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20D010 EU4209050 4LBSLI
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2115.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839235
CATALOG NUMBER: LD4C20D010 EU4209050 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839235

CATALOG NUMBER: LD4C20D010 EU4209050 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	185533
5°	181334
10°	170282
15°	158424
20°	146936
25°	133941
30°	119247
35°	105688
40°	94989
45°	85029
50°	72934
55°	58666
60°	43711
65°	27907
70°	13434
75°	2231
80°	1627
85°	0



TEST NUMBER: P839235

CATALOG NUMBER: LD4C20D010 EU4209050 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.9	6.5
10°-20°	349.2	16.5
20°-30°	452.6	21.4
30°-40°	443.4	21.0
40°-50°	375.8	17.8
50°-60°	246.4	11.6
60°-70°	99.0	4.7
70°-80°	11.3	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.7	44.4
0°-40°	1382.1	65.3
0°-60°	2004.3	94.8
0°-90°	2115.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2115.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1510	
5°	1470	137
15°	1246	349
25°	988	453
35°	705	443
45°	489	376
55°	274	246
65°	96	99
75°	5	11
85°	0	0
90°	0	



TEST NUMBER: P839235

CATALOG NUMBER: LD4C20D010 EU4209050 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1510.2
2.5°	1498.5
5°	1470.4
7.5°	1423.5
10°	1365.0
12.5°	1301.8
15°	1245.6
17.5°	1184.7
20°	1123.9
22.5°	1058.3
25°	988.1
27.5°	915.5
30°	840.6
32.5°	770.3
35°	704.7
37.5°	650.9
40°	592.3
42.5°	540.9
45°	489.4
47.5°	435.5
50°	381.6
52.5°	327.8
55°	273.9
57.5°	224.8
60°	177.9
62.5°	135.8
65°	96.0
67.5°	63.2
70°	37.4
72.5°	16.4
75°	4.7
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)