

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839675

Luminaire Tested: **LDS4C100D010 EU41009035 4LBSWMH**

Issue Date: 8/24/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P839675  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C100D010 EU41009035 4LBSWMH  
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBS TRIM WITH WMH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8962.0 lumens  
Efficiency: N/A  
Efficacy: 78.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 114.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839675

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBSWMH

### Luminous Intensity Polar Plot





TEST NUMBER: P839675

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBSWMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	575827
5°	573155
10°	561319
15°	540927
20°	516023
25°	488211
30°	460531
35°	433612
40°	408280
45°	380580
50°	347028
55°	306482
60°	259417
65°	203662
70°	145368
75°	79650
80°	14008
85°	0



TEST NUMBER: P839675

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBSWMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	439.0	4.9
10°-20°	1193.3	13.3
20°-30°	1657.2	18.5
30°-40°	1808.4	20.2
40°-50°	1686.9	18.8
50°-60°	1280.4	14.3
60°-70°	701.1	7.8
70°-80°	192.9	2.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3289.5	36.7
0°-40°	5097.9	56.9
0°-60°	8065.3	90.0
0°-90°	8962.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8962.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4687	
5°	4648	439
15°	4253	1193
25°	3602	1657
35°	2891	1808
45°	2190	1687
55°	1431	1280
65°	701	701
75°	168	193
85°	0	3
90°	0	



TEST NUMBER: P839675

CATALOG NUMBER: LDS4C100D010 EU41009035 4LBSWMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4687.1
2.5°	4687.1
5°	4647.6
7.5°	4588.6
10°	4499.6
12.5°	4381.3
15°	4253.0
17.5°	4095.2
20°	3947.0
22.5°	3769.4
25°	3601.6
27.5°	3434.0
30°	3246.4
32.5°	3068.8
35°	2891.2
37.5°	2713.6
40°	2545.8
42.5°	2368.2
45°	2190.5
47.5°	2012.9
50°	1815.7
52.5°	1628.1
55°	1430.9
57.5°	1243.2
60°	1055.8
62.5°	868.4
65°	700.6
67.5°	542.6
70°	404.7
72.5°	276.3
75°	167.8
77.5°	78.9
80°	19.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)