

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839239

Luminaire Tested: **LD4C25D010 EU4259030 4LBPSMW**

Issue Date: 6/29/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P839239  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C25D010 EU4259030 4LBPSMW  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBPS TRIM WITH MW FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2455.0 lumens  
Efficiency: N/A  
Efficacy: 77.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839239

CATALOG NUMBER: LD4C25D010 EU4259030 4LBPSMW

### Luminous Intensity Polar Plot





TEST NUMBER: P839239

CATALOG NUMBER: LD4C25D010 EU4259030 4LBPSMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	141453
5°	141217
10°	140455
15°	138825
20°	136307
25°	133358
30°	130184
35°	126460
40°	121371
45°	112584
50°	96996
55°	77365
60°	60247
65°	45087
70°	32723
75°	25964
80°	24337
85°	24245



TEST NUMBER: P839239

CATALOG NUMBER: LD4C25D010 EU4259030 4LBPSMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.7	4.4
10°-20°	307.4	12.5
20°-30°	453.0	18.5
30°-40°	526.2	21.4
40°-50°	494.6	20.1
50°-60°	327.4	13.3
60°-70°	157.8	6.4
70°-80°	60.8	2.5
80°-90°	19.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	869.1	35.4
0°-40°	1395.3	56.8
0°-60°	2217.4	90.3
0°-90°	2455.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2455.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1151	
5°	1145	109
15°	1092	307
25°	984	453
35°	843	526
45°	648	495
55°	361	327
65°	155	158
75°	55	61
85°	17	19
90°	0	



TEST NUMBER: P839239

CATALOG NUMBER: LD4C25D010 EU4259030 4LBPSMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1151.4
2.5°	1150.3
5°	1145.1
7.5°	1137.3
10°	1125.9
12.5°	1110.2
15°	1091.5
17.5°	1068.6
20°	1042.6
22.5°	1014.0
25°	983.8
27.5°	951.5
30°	917.7
32.5°	881.7
35°	843.2
37.5°	801.1
40°	756.8
42.5°	706.9
45°	648.0
47.5°	581.4
50°	507.5
52.5°	432.5
55°	361.2
57.5°	299.8
60°	245.2
62.5°	196.2
65°	155.1
67.5°	120.2
70°	91.1
72.5°	69.2
75°	54.7
77.5°	44.2
80°	34.4
82.5°	25.5
85°	17.2
87.5°	9.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)