

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839679

Luminaire Tested: **LDS4C100D010 EU41009040 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C100D010 EU41009040 4LBPSMMS
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8260.0 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839679

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839679

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	532840
5°	531015
10°	525180
15°	516139
20°	504583
25°	491098
30°	475625
35°	457308
40°	434244
45°	394809
50°	325946
55°	240020
60°	162904
65°	95377
70°	37680
75°	8497
80°	11037
85°	18888



TEST NUMBER: P839679

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	408.0	4.9
10°-20°	1142.7	13.8
20°-30°	1666.8	20.2
30°-40°	1902.5	23.0
40°-50°	1729.6	20.9
50°-60°	1020.1	12.4
60°-70°	342.1	4.1
70°-80°	35.7	0.4
80°-90°	12.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3217.4	39.0
0°-40°	5120.0	62.0
0°-60°	7869.7	95.3
0°-90°	8260.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8260.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4337	
5°	4306	408
15°	4058	1143
25°	3623	1667
35°	3049	1903
45°	2272	1730
55°	1121	1020
65°	328	342
75°	18	36
85°	13	12
90°	0	



TEST NUMBER: P839679

CATALOG NUMBER: LDS4C100D010 EU41009040 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4337.2
2.5°	4330.5
5°	4305.9
7.5°	4265.7
10°	4209.9
12.5°	4138.5
15°	4058.1
17.5°	3964.4
20°	3859.5
22.5°	3745.6
25°	3622.9
27.5°	3488.9
30°	3352.8
32.5°	3203.2
35°	3049.2
37.5°	2881.8
40°	2707.7
42.5°	2504.5
45°	2272.4
47.5°	2004.5
50°	1705.4
52.5°	1406.3
55°	1120.6
57.5°	877.3
60°	663.0
62.5°	479.9
65°	328.1
67.5°	200.9
70°	104.9
72.5°	40.2
75°	17.9
77.5°	17.9
80°	15.6
82.5°	13.4
85°	13.4
87.5°	11.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)