

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839248

Luminaire Tested: **LD4C25D010 EU4259050 4LBPSMW**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25D010 EU4259050 4LBPSMW
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2545.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839248

CATALOG NUMBER: LD4C25D010 EU4259050 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839248

CATALOG NUMBER: LD4C25D010 EU4259050 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146638
5°	146396
10°	145594
15°	143912
20°	141302
25°	138238
30°	134950
35°	131094
40°	125829
45°	116719
50°	100551
55°	80214
60°	62434
65°	46744
70°	33908
75°	26914
80°	25186
85°	25091



TEST NUMBER: P839248

CATALOG NUMBER: LD4C25D010 EU4259050 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	4.4
10°-20°	318.7	12.5
20°-30°	469.6	18.5
30°-40°	545.5	21.4
40°-50°	512.8	20.1
50°-60°	339.4	13.3
60°-70°	163.5	6.4
70°-80°	63.1	2.5
80°-90°	19.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	901.0	35.4
0°-40°	1446.5	56.8
0°-60°	2298.7	90.3
0°-90°	2545.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2545.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1194	
5°	1187	113
15°	1132	319
25°	1020	470
35°	874	546
45°	672	513
55°	374	339
65°	161	164
75°	57	63
85°	18	20
90°	0	



TEST NUMBER: P839248

CATALOG NUMBER: LD4C25D010 EU4259050 4LBPSMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1193.6
2.5°	1192.5
5°	1187.1
7.5°	1179.0
10°	1167.1
12.5°	1150.9
15°	1131.5
17.5°	1107.8
20°	1080.8
22.5°	1051.1
25°	1019.8
27.5°	986.4
30°	951.3
32.5°	914.1
35°	874.1
37.5°	830.4
40°	784.6
42.5°	732.8
45°	671.8
47.5°	602.7
50°	526.1
52.5°	448.4
55°	374.5
57.5°	310.8
60°	254.1
62.5°	203.4
65°	160.8
67.5°	124.6
70°	94.4
72.5°	71.8
75°	56.7
77.5°	45.9
80°	35.6
82.5°	26.4
85°	17.8
87.5°	10.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)