

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839699

Luminaire Tested: **LDS4C10D010 EU4109027 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839699
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C10D010 EU4109027 4LBPSMMS
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 778.0 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839699

CATALOG NUMBER: LDS4C10D010 EU4109027 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839699

CATALOG NUMBER: LDS4C10D010 EU4109027 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50186
5°	50020
10°	49463
15°	48611
20°	47523
25°	46251
30°	44799
35°	43073
40°	40895
45°	37181
50°	30695
55°	22597
60°	15332
65°	8983
70°	3556
75°	807
80°	1061
85°	1832



TEST NUMBER: P839699

CATALOG NUMBER: LDS4C10D010 EU4109027 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.4	4.9
10°-20°	107.6	13.8
20°-30°	157.0	20.2
30°-40°	179.2	23.0
40°-50°	162.9	20.9
50°-60°	96.1	12.3
60°-70°	32.2	4.1
70°-80°	3.4	0.4
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	303.0	39.0
0°-40°	482.2	62.0
0°-60°	741.2	95.3
0°-90°	778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	408	
5°	406	38
15°	382	108
25°	341	157
35°	287	179
45°	214	163
55°	106	96
65°	31	32
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839699

CATALOG NUMBER: LDS4C10D010 EU4109027 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	408.5
2.5°	407.9
5°	405.6
7.5°	401.8
10°	396.5
12.5°	389.8
15°	382.2
17.5°	373.4
20°	363.5
22.5°	352.8
25°	341.2
27.5°	328.6
30°	315.8
32.5°	301.7
35°	287.2
37.5°	271.4
40°	255.0
42.5°	235.9
45°	214.0
47.5°	188.8
50°	160.6
52.5°	132.5
55°	105.5
57.5°	82.6
60°	62.4
62.5°	45.2
65°	30.9
67.5°	18.9
70°	9.9
72.5°	3.8
75°	1.7
77.5°	1.7
80°	1.5
82.5°	1.3
85°	1.3
87.5°	1.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)