

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839253

Luminaire Tested: **LD4C30D010 EU4309027 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30D010 EU4309027 4LBSLI
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2895.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839253

CATALOG NUMBER: LD4C30D010 EU4309027 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839253

CATALOG NUMBER: LD4C30D010 EU4309027 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90	90	90	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80	80	80	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71	71	71	71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63	63	63	63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57	57	57	57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51	51	51	51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46	46	46	46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42	42	42	42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	39	39	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36	36	36	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253950
5°	248199
10°	233080
15°	216854
20°	201114
25°	183337
30°	163223
35°	144667
40°	130031
45°	116372
50°	99844
55°	80321
60°	59830
65°	38197
70°	18427
75°	3038
80°	2264
85°	0



TEST NUMBER: P839253

CATALOG NUMBER: LD4C30D010 EU4309027 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.4	6.5
10°-20°	478.0	16.5
20°-30°	619.4	21.4
30°-40°	606.9	21.0
40°-50°	514.4	17.8
50°-60°	337.3	11.6
60°-70°	135.5	4.7
70°-80°	15.5	0.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1284.9	44.4
0°-40°	1891.8	65.3
0°-60°	2743.5	94.8
0°-90°	2895.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2895.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2067	
5°	2013	187
15°	1705	478
25°	1352	619
35°	965	607
45°	670	514
55°	375	337
65°	131	136
75°	6	15
85°	0	0
90°	0	



TEST NUMBER: P839253

CATALOG NUMBER: LD4C30D010 EU4309027 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2067.1
2.5°	2051.1
5°	2012.6
7.5°	1948.5
10°	1868.4
12.5°	1781.9
15°	1705.0
17.5°	1621.7
20°	1538.3
22.5°	1448.6
25°	1352.5
27.5°	1253.1
30°	1150.6
32.5°	1054.4
35°	964.6
37.5°	891.0
40°	810.8
42.5°	740.3
45°	669.8
47.5°	596.1
50°	522.4
52.5°	448.7
55°	375.0
57.5°	307.7
60°	243.5
62.5°	185.9
65°	131.4
67.5°	86.5
70°	51.3
72.5°	22.4
75°	6.4
77.5°	3.2
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)