

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839708

Luminaire Tested: **LDS4C10D010 EU4109030 4LBPSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C10D010 EU4109030 4LBPSMB
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 791.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839708

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839708

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51021
5°	50846
10°	50299
15°	49425
20°	48321
25°	47024
30°	45551
35°	43793
40°	41585
45°	37806
50°	31211
55°	22982
60°	15602
65°	9128
70°	3592
75°	807
80°	1061
85°	1832



TEST NUMBER: P839708

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.1	4.9
10°-20°	109.4	13.8
20°-30°	159.6	20.2
30°-40°	182.2	23.0
40°-50°	165.6	20.9
50°-60°	97.7	12.4
60°-70°	32.8	4.1
70°-80°	3.4	0.4
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	308.1	39.0
0°-40°	490.3	62.0
0°-60°	753.6	95.3
0°-90°	791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	791.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	415	
5°	412	39
15°	389	109
25°	347	160
35°	292	182
45°	218	166
55°	107	98
65°	31	33
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839708

CATALOG NUMBER: LDS4C10D010 EU4109030 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	415.3
2.5°	414.7
5°	412.3
7.5°	408.5
10°	403.2
12.5°	396.3
15°	388.6
17.5°	379.6
20°	369.6
22.5°	358.7
25°	346.9
27.5°	334.1
30°	321.1
32.5°	306.7
35°	292.0
37.5°	276.0
40°	259.3
42.5°	239.8
45°	217.6
47.5°	192.0
50°	163.3
52.5°	134.7
55°	107.3
57.5°	84.0
60°	63.5
62.5°	46.0
65°	31.4
67.5°	19.2
70°	10.0
72.5°	3.8
75°	1.7
77.5°	1.7
80°	1.5
82.5°	1.3
85°	1.3
87.5°	1.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)