

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839268

Luminaire Tested: **LD4C35D010 EU4359027 4LBSLI**

Issue Date: 2/9/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839268  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C35D010 EU4359027 4LBSLI  
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3417.0 lumens  
Efficiency: N/A  
Efficacy: 84.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839268

CATALOG NUMBER: LD4C35D010 EU4359027 4LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839268

CATALOG NUMBER: LD4C35D010 EU4359027 4LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	299750
5°	292953
10°	275108
15°	255952
20°	237381
25°	216385
30°	192644
35°	170763
40°	153478
45°	137360
50°	117848
55°	94800
60°	70641
65°	45087
70°	21732
75°	3607
80°	2688
85°	0



TEST NUMBER: P839268

CATALOG NUMBER: LD4C35D010 EU4359027 4LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.2	6.5
10°-20°	564.2	16.5
20°-30°	731.1	21.4
30°-40°	716.4	21.0
40°-50°	607.2	17.8
50°-60°	398.0	11.6
60°-70°	160.0	4.7
70°-80°	18.3	0.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1516.6	44.4
0°-40°	2232.9	65.3
0°-60°	3238.2	94.8
0°-90°	3417.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3417.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2440	
5°	2376	221
15°	2012	564
25°	1596	731
35°	1139	716
45°	791	607
55°	443	398
65°	155	160
75°	8	18
85°	0	1
90°	0	



TEST NUMBER: P839268

CATALOG NUMBER: LD4C35D010 EU4359027 4LBSLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2439.9
2.5°	2420.9
5°	2375.5
7.5°	2299.8
10°	2205.3
12.5°	2103.2
15°	2012.4
17.5°	1914.1
20°	1815.7
22.5°	1709.8
25°	1596.3
27.5°	1479.0
30°	1358.0
32.5°	1244.5
35°	1138.6
37.5°	1051.6
40°	957.0
42.5°	873.8
45°	790.6
47.5°	703.6
50°	616.6
52.5°	529.6
55°	442.6
57.5°	363.1
60°	287.5
62.5°	219.4
65°	155.1
67.5°	102.1
70°	60.5
72.5°	26.5
75°	7.6
77.5°	3.8
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)