

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839326

Luminaire Tested: **LD4C55D010 EU4559027 4LBPSMW**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C55D010 EU4559027 4LBPSMW
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5567.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839326

CATALOG NUMBER: LD4C55D010 EU4559027 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839326

CATALOG NUMBER: LD4C55D010 EU4559027 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	320758
5°	320232
10°	318483
15°	314801
20°	309091
25°	302393
30°	295194
35°	286770
40°	275234
45°	255312
50°	219948
55°	175442
60°	136588
65°	102238
70°	74211
75°	58812
80°	55113
85°	54974



TEST NUMBER: P839326

CATALOG NUMBER: LD4C55D010 EU4559027 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.5	4.4
10°-20°	697.0	12.5
20°-30°	1027.2	18.5
30°-40°	1193.3	21.4
40°-50°	1121.7	20.1
50°-60°	742.5	13.3
60°-70°	357.8	6.4
70°-80°	138.0	2.5
80°-90°	43.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1970.8	35.4
0°-40°	3164.1	56.8
0°-60°	5028.2	90.3
0°-90°	5567.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5567.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2611	
5°	2597	247
15°	2475	697
25°	2231	1027
35°	1912	1193
45°	1470	1122
55°	819	742
65°	352	358
75°	124	138
85°	39	43
90°	0	



TEST NUMBER: P839326

CATALOG NUMBER: LD4C55D010 EU4559027 4LBPSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2610.9
2.5°	2608.5
5°	2596.7
7.5°	2579.0
10°	2553.0
12.5°	2517.6
15°	2475.1
17.5°	2423.2
20°	2364.2
22.5°	2299.3
25°	2230.8
27.5°	2157.6
30°	2080.9
32.5°	1999.5
35°	1912.1
37.5°	1816.5
40°	1716.2
42.5°	1602.9
45°	1469.5
47.5°	1318.4
50°	1150.8
52.5°	980.8
55°	819.1
57.5°	679.9
60°	555.9
62.5°	445.0
65°	351.7
67.5°	272.7
70°	206.6
72.5°	157.0
75°	123.9
77.5°	100.3
80°	77.9
82.5°	57.8
85°	39.0
87.5°	22.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)