

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839733

Luminaire Tested: **LDS4C10D010 EU4109040 4LBSLI**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839733  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C10D010 EU4109040 4LBSLI  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1049.0 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839733

CATALOG NUMBER: LDS4C10D010 EU4109040 4LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839733

CATALOG NUMBER: LDS4C10D010 EU4109040 4LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92017
5°	89939
10°	84455
15°	78576
20°	72873
25°	66435
30°	59141
35°	52417
40°	47118
45°	42167
50°	36180
55°	29108
60°	21671
65°	13837
70°	6681
75°	1092
80°	849
85°	0



TEST NUMBER: P839733

CATALOG NUMBER: LDS4C10D010 EU4109040 4LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.9	6.5
10°-20°	173.2	16.5
20°-30°	224.4	21.4
30°-40°	219.9	21.0
40°-50°	186.4	17.8
50°-60°	122.2	11.6
60°-70°	49.1	4.7
70°-80°	5.6	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.6	44.4
0°-40°	685.5	65.3
0°-60°	994.1	94.8
0°-90°	1049.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	749	
5°	729	68
15°	618	173
25°	490	224
35°	350	220
45°	243	186
55°	136	122
65°	48	49
75°	2	6
85°	0	0
90°	0	



TEST NUMBER: P839733

CATALOG NUMBER: LDS4C10D010 EU4109040 4LBSLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	749.0
2.5°	743.2
5°	729.3
7.5°	706.0
10°	677.0
12.5°	645.7
15°	617.8
17.5°	587.6
20°	557.4
22.5°	524.9
25°	490.1
27.5°	454.0
30°	416.9
32.5°	382.1
35°	349.5
37.5°	322.8
40°	293.8
42.5°	268.3
45°	242.7
47.5°	216.0
50°	189.3
52.5°	162.6
55°	135.9
57.5°	111.5
60°	88.2
62.5°	67.3
65°	47.6
67.5°	31.4
70°	18.6
72.5°	8.1
75°	2.3
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)