

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839739

Luminaire Tested: **LDS4C10D010 EU4109050 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C10D010 EU4109050 4LBPSMMS
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 838.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839739

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839739

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54056
5°	53867
10°	53280
15°	52363
20°	51197
25°	49830
30°	48246
35°	46388
40°	44055
45°	40047
50°	33065
55°	24353
60°	16536
65°	9680
70°	3808
75°	854
80°	1132
85°	1973



TEST NUMBER: P839739

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.4	4.9
10°-20°	115.9	13.8
20°-30°	169.1	20.2
30°-40°	193.0	23.0
40°-50°	175.5	20.9
50°-60°	103.5	12.4
60°-70°	34.7	4.1
70°-80°	3.6	0.4
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.4	39.0
0°-40°	519.4	62.0
0°-60°	798.4	95.3
0°-90°	838.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	440	
5°	437	41
15°	412	116
25°	368	169
35°	309	193
45°	230	175
55°	114	104
65°	33	35
75°	2	4
85°	1	1
90°	0	



TEST NUMBER: P839739

CATALOG NUMBER: LDS4C10D010 EU4109050 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	440.0
2.5°	439.3
5°	436.8
7.5°	432.8
10°	427.1
12.5°	419.9
15°	411.7
17.5°	402.2
20°	391.6
22.5°	380.0
25°	367.6
27.5°	354.0
30°	340.1
32.5°	325.0
35°	309.3
37.5°	292.4
40°	274.7
42.5°	254.1
45°	230.5
47.5°	203.4
50°	173.0
52.5°	142.7
55°	113.7
57.5°	89.0
60°	67.3
62.5°	48.7
65°	33.3
67.5°	20.4
70°	10.6
72.5°	4.1
75°	1.8
77.5°	1.8
80°	1.6
82.5°	1.4
85°	1.4
87.5°	1.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)