

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839756

Luminaire Tested: **LDS4C15D010 EU4159030 4LBCSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159030 4LBCSMB
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1067.0 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839756

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839756

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68835
5°	68592
10°	67838
15°	66672
20°	65186
25°	63439
30°	61439
35°	59076
40°	56099
45°	50993
50°	42105
55°	31014
60°	21033
65°	12326
70°	4885
75°	1092
80°	1415
85°	2396



TEST NUMBER: P839756

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	4.9
10°-20°	147.6	13.8
20°-30°	215.3	20.2
30°-40°	245.8	23.0
40°-50°	223.4	20.9
50°-60°	131.8	12.4
60°-70°	44.2	4.1
70°-80°	4.6	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.6	39.0
0°-40°	661.4	62.0
0°-60°	1016.6	95.3
0°-90°	1067.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1067.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	556	53
15°	524	148
25°	468	215
35°	394	246
45°	294	223
55°	145	132
65°	42	44
75°	2	5
85°	2	2
90°	0	



TEST NUMBER: P839756

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	560.3
2.5°	559.4
5°	556.2
7.5°	551.0
10°	543.8
12.5°	534.6
15°	524.2
17.5°	512.1
20°	498.6
22.5°	483.8
25°	468.0
27.5°	450.7
30°	433.1
32.5°	413.8
35°	393.9
37.5°	372.3
40°	349.8
42.5°	323.5
45°	293.5
47.5°	258.9
50°	220.3
52.5°	181.7
55°	144.8
57.5°	113.3
60°	85.6
62.5°	62.0
65°	42.4
67.5°	26.0
70°	13.6
72.5°	5.2
75°	2.3
77.5°	2.3
80°	2.0
82.5°	1.7
85°	1.7
87.5°	1.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)