

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839379

Luminaire Tested: **LD4C70D010 EU4709035 4LBSLI**

Issue Date: 2/9/2022

Test Information

Test Method: LM-79-08
Report Number: P839379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C70D010 EU4709035 4LBSLI
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7279.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839379

CATALOG NUMBER: LD4C70D010 EU4709035 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839379

CATALOG NUMBER: LD4C70D010 EU4709035 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	638531
5°	624062
10°	586044
15°	545226
20°	505681
25°	460964
30°	410384
35°	363753
40°	326938
45°	292615
50°	251025
55°	201937
60°	150471
65°	96046
70°	46301
75°	7690
80°	5660
85°	0



TEST NUMBER: P839379

CATALOG NUMBER: LD4C70D010 EU4709035 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	471.3	6.5
10°-20°	1201.9	16.5
20°-30°	1557.5	21.4
30°-40°	1526.0	21.0
40°-50°	1293.5	17.8
50°-60°	847.9	11.6
60°-70°	340.8	4.7
70°-80°	39.0	0.5
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3230.7	44.4
0°-40°	4756.7	65.3
0°-60°	6898.1	94.8
0°-90°	7279.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7279.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5198	
5°	5060	471
15°	4287	1202
25°	3401	1557
35°	2425	1526
45°	1684	1293
55°	943	848
65°	330	341
75°	16	39
85°	0	1
90°	0	



TEST NUMBER: P839379

CATALOG NUMBER: LD4C70D010 EU4709035 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5197.5
2.5°	5157.1
5°	5060.4
7.5°	4899.2
10°	4697.8
12.5°	4480.2
15°	4286.8
17.5°	4077.4
20°	3867.9
22.5°	3642.3
25°	3400.6
27.5°	3150.6
30°	2892.9
32.5°	2651.2
35°	2425.4
37.5°	2240.2
40°	2038.6
42.5°	1861.4
45°	1684.2
47.5°	1498.8
50°	1313.4
52.5°	1128.2
55°	942.8
57.5°	773.6
60°	612.4
62.5°	467.3
65°	330.4
67.5°	217.6
70°	128.9
72.5°	56.3
75°	16.2
77.5°	8.0
80°	8.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)