

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839758

Luminaire Tested: **LDS4C15D010 EU4159030 4LBPSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159030 4LBPSMB
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1211.9 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839758

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839758

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78184
5°	77915
10°	77057
15°	75740
20°	74037
25°	72060
30°	69795
35°	67099
40°	63717
45°	57925
50°	47820
55°	35213
60°	23907
65°	13982
70°	5532
75°	1234
80°	1627
85°	2819



TEST NUMBER: P839758

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.9	4.9
10°-20°	167.7	13.8
20°-30°	244.6	20.2
30°-40°	279.2	23.0
40°-50°	253.8	20.9
50°-60°	149.7	12.3
60°-70°	50.2	4.1
70°-80°	5.2	0.4
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	472.1	39.0
0°-40°	751.2	62.0
0°-60°	1154.7	95.3
0°-90°	1211.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1211.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	636	
5°	632	60
15°	596	168
25°	532	245
35°	447	279
45°	333	254
55°	164	150
65°	48	50
75°	3	5
85°	2	2
90°	0	



TEST NUMBER: P839758

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	636.4
2.5°	635.4
5°	631.8
7.5°	625.9
10°	617.7
12.5°	607.2
15°	595.5
17.5°	581.7
20°	566.3
22.5°	549.6
25°	531.6
27.5°	511.9
30°	492.0
32.5°	470.0
35°	447.4
37.5°	422.8
40°	397.3
42.5°	367.5
45°	333.4
47.5°	294.1
50°	250.2
52.5°	206.3
55°	164.4
57.5°	128.7
60°	97.3
62.5°	70.4
65°	48.1
67.5°	29.5
70°	15.4
72.5°	5.9
75°	2.6
77.5°	2.6
80°	2.3
82.5°	2.0
85°	2.0
87.5°	1.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)