

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839384

Luminaire Tested: **LD4C70D010 EU4709050 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P839384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C70D010 EU4709050 4LBSH
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7133.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839384

CATALOG NUMBER: LD4C70D010 EU4709050 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839384

CATALOG NUMBER: LD4C70D010 EU4709050 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	458305
5°	456183
10°	446762
15°	430529
20°	410713
25°	388579
30°	366535
35°	345111
40°	324949
45°	302918
50°	276215
55°	243939
60°	206492
65°	162092
70°	115698
75°	63416
80°	11178
85°	0



TEST NUMBER: P839384

CATALOG NUMBER: LD4C70D010 EU4709050 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.4	4.9
10°-20°	949.8	13.3
20°-30°	1319.0	18.5
30°-40°	1439.3	20.2
40°-50°	1342.6	18.8
50°-60°	1019.1	14.3
60°-70°	558.0	7.8
70°-80°	153.6	2.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2618.2	36.7
0°-40°	4057.5	56.9
0°-60°	6419.3	90.0
0°-90°	7133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3730	
5°	3699	349
15°	3385	950
25°	2867	1319
35°	2301	1439
45°	1744	1343
55°	1139	1019
65°	558	558
75°	134	154
85°	0	2
90°	0	



TEST NUMBER: P839384

CATALOG NUMBER: LD4C70D010 EU4709050 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3730.5
2.5°	3730.5
5°	3699.1
7.5°	3652.1
10°	3581.3
12.5°	3487.2
15°	3385.0
17.5°	3259.4
20°	3141.5
22.5°	3000.1
25°	2866.6
27.5°	2733.2
30°	2583.8
32.5°	2442.5
35°	2301.1
37.5°	2159.8
40°	2026.2
42.5°	1884.8
45°	1743.5
47.5°	1602.1
50°	1445.2
52.5°	1295.8
55°	1138.9
57.5°	989.5
60°	840.4
62.5°	691.2
65°	557.6
67.5°	431.9
70°	322.1
72.5°	219.9
75°	133.6
77.5°	62.8
80°	15.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)