

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839762

Luminaire Tested: **LDS4C15D010 EU4159030 4LBSH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159030 4LBSH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1517.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839762

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839762

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97472
5°	97018
10°	95021
15°	91562
20°	87346
25°	82634
30°	77952
35°	73398
40°	69105
45°	64423
50°	58733
55°	51876
60°	43908
65°	34477
70°	24605
75°	13481
80°	2405
85°	0



TEST NUMBER: P839762

CATALOG NUMBER: LDS4C15D010 EU4159030 4LSBH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.3	4.9
10°-20°	202.0	13.3
20°-30°	280.5	18.5
30°-40°	306.1	20.2
40°-50°	285.5	18.8
50°-60°	216.7	14.3
60°-70°	118.7	7.8
70°-80°	32.7	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.8	36.7
0°-40°	862.9	56.9
0°-60°	1365.2	90.0
0°-90°	1517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	793	
5°	787	74
15°	720	202
25°	610	281
35°	489	306
45°	371	286
55°	242	217
65°	119	119
75°	28	33
85°	0	0
90°	0	



TEST NUMBER: P839762

CATALOG NUMBER: LDS4C15D010 EU4159030 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	793.4
2.5°	793.4
5°	786.7
7.5°	776.7
10°	761.7
12.5°	741.6
15°	719.9
17.5°	693.2
20°	668.1
22.5°	638.0
25°	609.6
27.5°	581.3
30°	549.5
32.5°	519.5
35°	489.4
37.5°	459.3
40°	430.9
42.5°	400.9
45°	370.8
47.5°	340.7
50°	307.3
52.5°	275.6
55°	242.2
57.5°	210.4
60°	178.7
62.5°	147.0
65°	118.6
67.5°	91.8
70°	68.5
72.5°	46.8
75°	28.4
77.5°	13.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)