

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839766

Luminaire Tested: **LDS4C15D010 EU4159035 4LBCSMB**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159035 4LBCSMB
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1082.0 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839766

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839766

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69793
5°	69554
10°	68799
15°	67613
20°	66101
25°	64334
30°	62304
35°	59901
40°	56885
45°	51723
50°	42698
55°	31443
60°	21327
65°	12500
70°	4921
75°	1092
80°	1415
85°	2537



TEST NUMBER: P839766

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	4.9
10°-20°	149.7	13.8
20°-30°	218.3	20.2
30°-40°	249.2	23.0
40°-50°	226.6	20.9
50°-60°	133.6	12.3
60°-70°	44.8	4.1
70°-80°	4.7	0.4
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	421.5	39.0
0°-40°	670.7	62.0
0°-60°	1030.9	95.3
0°-90°	1082.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1082.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	568	
5°	564	53
15°	532	150
25°	475	218
35°	399	249
45°	298	227
55°	147	134
65°	43	45
75°	2	5
85°	2	2
90°	0	



TEST NUMBER: P839766

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	568.1
2.5°	567.3
5°	564.0
7.5°	558.8
10°	551.5
12.5°	542.1
15°	531.6
17.5°	519.3
20°	505.6
22.5°	490.7
25°	474.6
27.5°	457.0
30°	439.2
32.5°	419.6
35°	399.4
37.5°	377.5
40°	354.7
42.5°	328.1
45°	297.7
47.5°	262.6
50°	223.4
52.5°	184.2
55°	146.8
57.5°	114.9
60°	86.8
62.5°	62.9
65°	43.0
67.5°	26.3
70°	13.7
72.5°	5.3
75°	2.3
77.5°	2.3
80°	2.0
82.5°	1.8
85°	1.8
87.5°	1.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)