

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839770

Luminaire Tested: **LDS4C15D010 EU4159035 4LBSB**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839770  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C15D010 EU4159035 4LBSB  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBS TRIM WITH B FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 845.0 lumens  
Efficiency: N/A  
Efficacy: 53.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839770

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSB

### Luminous Intensity Polar Plot





TEST NUMBER: P839770

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54510
5°	54324
10°	53729
15°	52795
20°	51615
25°	50236
30°	48658
35°	46778
40°	44424
45°	40395
50°	33352
55°	24546
60°	16659
65°	9767
70°	3843
75°	854
80°	1132
85°	1973



TEST NUMBER: P839770

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.7	4.9
10°-20°	116.9	13.8
20°-30°	170.5	20.2
30°-40°	194.6	23.0
40°-50°	177.0	20.9
50°-60°	104.3	12.3
60°-70°	35.0	4.1
70°-80°	3.6	0.4
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.1	39.0
0°-40°	523.8	62.0
0°-60°	805.1	95.3
0°-90°	845.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	444	
5°	440	42
15°	415	117
25°	371	171
35°	312	195
45°	232	177
55°	115	104
65°	34	35
75°	2	4
85°	1	1
90°	0	



TEST NUMBER: P839770

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	443.7
2.5°	443.0
5°	440.5
7.5°	436.4
10°	430.7
12.5°	423.4
15°	415.1
17.5°	405.6
20°	394.8
22.5°	383.2
25°	370.6
27.5°	356.9
30°	343.0
32.5°	327.7
35°	311.9
37.5°	294.8
40°	277.0
42.5°	256.2
45°	232.5
47.5°	205.1
50°	174.5
52.5°	143.9
55°	114.6
57.5°	89.7
60°	67.8
62.5°	49.1
65°	33.6
67.5°	20.6
70°	10.7
72.5°	4.1
75°	1.8
77.5°	1.8
80°	1.6
82.5°	1.4
85°	1.4
87.5°	1.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)