

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839420

Luminaire Tested: **LD4C90D010 EU4909030 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P839420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C90D010 EU4909030 4LBSH
Description: 4 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9309.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839420

CATALOG NUMBER: LD4C90D010 EU4909030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839420

CATALOG NUMBER: LD4C90D010 EU4909030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	598112
5°	595353
10°	583063
15°	561863
20°	535999
25°	507107
30°	478363
35°	450394
40°	424076
45°	395330
50°	360464
55°	318348
60°	269467
65°	211540
70°	151007
75°	82735
80°	14574
85°	0



TEST NUMBER: P839420

CATALOG NUMBER: LD4C90D010 EU4909030 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	456.0	4.9
10°-20°	1239.5	13.3
20°-30°	1721.3	18.5
30°-40°	1878.4	20.2
40°-50°	1752.2	18.8
50°-60°	1330.0	14.3
60°-70°	728.2	7.8
70°-80°	200.4	2.2
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3416.9	36.7
0°-40°	5295.3	56.9
0°-60°	8377.5	90.0
0°-90°	9309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4868	
5°	4828	456
15°	4418	1240
25°	3741	1721
35°	3003	1878
45°	2275	1752
55°	1486	1330
65°	728	728
75°	174	200
85°	0	3
90°	0	



TEST NUMBER: P839420

CATALOG NUMBER: LD4C90D010 EU4909030 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4868.5
2.5°	4868.5
5°	4827.6
7.5°	4766.2
10°	4673.9
12.5°	4551.0
15°	4417.6
17.5°	4253.8
20°	4099.8
22.5°	3915.3
25°	3741.0
27.5°	3567.0
30°	3372.1
32.5°	3187.6
35°	3003.1
37.5°	2818.6
40°	2644.3
42.5°	2459.8
45°	2275.4
47.5°	2090.9
50°	1886.0
52.5°	1691.1
55°	1486.3
57.5°	1291.4
60°	1096.7
62.5°	902.0
65°	727.7
67.5°	563.6
70°	420.4
72.5°	287.0
75°	174.3
77.5°	81.9
80°	20.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)