

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839775

Luminaire Tested: **LDS4C15D010 EU4159035 4LBSWMH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159035 4LBSWMH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1366.0 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839775

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839775

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87767
5°	87362
10°	85553
15°	82443
20°	78652
25°	74419
30°	70192
35°	66095
40°	62225
45°	58012
50°	52904
55°	46715
60°	39534
65°	31046
70°	22163
75°	12152
80°	2122
85°	0



TEST NUMBER: P839775

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.9	4.9
10°-20°	181.9	13.3
20°-30°	252.6	18.5
30°-40°	275.6	20.2
40°-50°	257.1	18.8
50°-60°	195.2	14.3
60°-70°	106.9	7.8
70°-80°	29.4	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.4	36.7
0°-40°	777.0	56.9
0°-60°	1229.3	90.0
0°-90°	1366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1366.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	714	
5°	708	67
15°	648	182
25°	549	253
35°	441	276
45°	334	257
55°	218	195
65°	107	107
75°	26	29
85°	0	0
90°	0	



TEST NUMBER: P839775

CATALOG NUMBER: LDS4C15D010 EU4159035 4LBSWMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	714.4
2.5°	714.4
5°	708.4
7.5°	699.4
10°	685.8
12.5°	667.8
15°	648.2
17.5°	624.2
20°	601.6
22.5°	574.5
25°	549.0
27.5°	523.4
30°	494.8
32.5°	467.7
35°	440.7
37.5°	413.6
40°	388.0
42.5°	361.0
45°	333.9
47.5°	306.8
50°	276.8
52.5°	248.2
55°	218.1
57.5°	189.5
60°	160.9
62.5°	132.4
65°	106.8
67.5°	82.7
70°	61.7
72.5°	42.1
75°	25.6
77.5°	12.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)