

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839444

Luminaire Tested: **LD6C08D010 EU6089040 6LCSQWLI**

Issue Date: 6/29/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P839444  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C08D010 EU6089040 6LCSQWLI  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 6LCSQW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 901.0 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839444

CATALOG NUMBER: LD6C08D010 EU6089040 6LCSQWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839444

CATALOG NUMBER: LD6C08D010 EU6089040 6LCSQWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18195
5°	18165
10°	18065
15°	17857
20°	17530
25°	17150
30°	16744
35°	16268
40°	15614
45°	14480
50°	12479
55°	9954
60°	7750
65°	5797
70°	4205
75°	3344
80°	3124
85°	3112



TEST NUMBER: P839444

CATALOG NUMBER: LD6C08D010 EU6089040 6LCSQWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.9	4.4
10°-20°	112.8	12.5
20°-30°	166.2	18.5
30°-40°	193.1	21.4
40°-50°	181.5	20.1
50°-60°	120.2	13.3
60°-70°	57.9	6.4
70°-80°	22.3	2.5
80°-90°	7.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	319.0	35.4
0°-40°	512.1	56.8
0°-60°	813.8	90.3
0°-90°	901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	901.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	423	
5°	420	40
15°	401	113
25°	361	166
35°	310	193
45°	238	182
55°	133	120
65°	57	58
75°	20	22
85°	6	7
90°	0	



TEST NUMBER: P839444

CATALOG NUMBER: LD6C08D010 EU6089040 6LCSQWLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	422.6
2.5°	422.2
5°	420.3
7.5°	417.4
10°	413.2
12.5°	407.5
15°	400.6
17.5°	392.2
20°	382.6
22.5°	372.1
25°	361.0
27.5°	349.2
30°	336.8
32.5°	323.6
35°	309.5
37.5°	294.0
40°	277.8
42.5°	259.4
45°	237.8
47.5°	213.4
50°	186.3
52.5°	158.7
55°	132.6
57.5°	110.0
60°	90.0
62.5°	72.0
65°	56.9
67.5°	44.1
70°	33.4
72.5°	25.4
75°	20.1
77.5°	16.2
80°	12.6
82.5°	9.4
85°	6.3
87.5°	3.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)