

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839776

Luminaire Tested: **LDS4C15D010 EU4159040 4LBCSMB**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839776  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C15D010 EU4159040 4LBCSMB  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBCS TRIM WITH MB FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1084.1 lumens  
Efficiency: N/A  
Efficacy: 68.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839776

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBCSMB

### Luminous Intensity Polar Plot





TEST NUMBER: P839776

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBCSMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	69928
5°	69690
10°	68924
15°	67740
20°	66219
25°	64442
30°	62418
35°	60021
40°	56981
45°	51810
50°	42774
55°	31507
60°	21377
65°	12529
70°	4957
75°	1092
80°	1486
85°	2537



TEST NUMBER: P839776

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBCSMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.5	4.9
10°-20°	150.0	13.8
20°-30°	218.7	20.2
30°-40°	249.7	23.0
40°-50°	227.0	20.9
50°-60°	133.9	12.4
60°-70°	44.9	4.1
70°-80°	4.7	0.4
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.2	38.9
0°-40°	671.9	62.0
0°-60°	1032.8	95.3
0°-90°	1084.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1084.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	569	
5°	565	54
15°	533	150
25°	475	219
35°	400	250
45°	298	227
55°	147	134
65°	43	45
75°	2	5
85°	2	2
90°	0	



TEST NUMBER: P839776

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBCSMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	569.2
2.5°	568.3
5°	565.1
7.5°	559.8
10°	552.5
12.5°	543.1
15°	532.6
17.5°	520.3
20°	506.5
22.5°	491.6
25°	475.4
27.5°	457.9
30°	440.0
32.5°	420.4
35°	400.2
37.5°	378.2
40°	355.3
42.5°	328.7
45°	298.2
47.5°	263.1
50°	223.8
52.5°	184.6
55°	147.1
57.5°	115.1
60°	87.0
62.5°	63.0
65°	43.1
67.5°	26.4
70°	13.8
72.5°	5.3
75°	2.3
77.5°	2.3
80°	2.1
82.5°	1.8
85°	1.8
87.5°	1.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)