

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839467

Luminaire Tested: **LD6C150D010 EU61509030 6LCSQWLI**

Issue Date: 6/29/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P839467  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C150D010 EU61509030 6LCSQWLI  
Description: 6 INCH 15000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LCSQW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16336.9 lumens  
Efficiency: N/A  
Efficacy: 95.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 171.1  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839467

CATALOG NUMBER: LD6C150D010 EU61509030 6LCSQWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839467

CATALOG NUMBER: LD6C150D010 EU61509030 6LCSQWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	329888
5°	329350
10°	327554
15°	323767
20°	317887
25°	311002
30°	303598
35°	294937
40°	283066
45°	262582
50°	226214
55°	180449
60°	140482
65°	105159
70°	76312
75°	60503
80°	56681
85°	56465



TEST NUMBER: P839467

CATALOG NUMBER: LD6C150D010 EU61509030 6LCSQWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	723.4	4.4
10°-20°	2045.6	12.5
20°-30°	3014.5	18.5
30°-40°	3501.8	21.4
40°-50°	3291.6	20.1
50°-60°	2178.9	13.3
60°-70°	1049.9	6.4
70°-80°	404.9	2.5
80°-90°	126.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5783.5	35.4
0°-40°	9285.3	56.8
0°-60°	14755.8	90.3
0°-90°	16336.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16336.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7662	
5°	7620	723
15°	7264	2046
25°	6546	3014
35°	5611	3502
45°	4312	3292
55°	2404	2179
65°	1032	1050
75°	364	405
85°	114	126
90°	0	



TEST NUMBER: P839467

CATALOG NUMBER: LD6C150D010 EU61509030 6LCSQWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7661.9
2.5°	7654.9
5°	7620.3
7.5°	7568.4
10°	7492.1
12.5°	7388.2
15°	7263.5
17.5°	7111.1
20°	6937.9
22.5°	6747.4
25°	6546.5
27.5°	6331.8
30°	6106.6
32.5°	5867.6
35°	5611.3
37.5°	5330.8
40°	5036.3
42.5°	4703.8
45°	4312.4
47.5°	3869.0
50°	3377.2
52.5°	2878.4
55°	2403.9
57.5°	1995.1
60°	1631.4
62.5°	1305.8
65°	1032.2
67.5°	800.1
70°	606.2
72.5°	460.7
75°	363.7
77.5°	294.4
80°	228.6
82.5°	169.7
85°	114.3
87.5°	65.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)