

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839784

Luminaire Tested: **LDS4C15D010 EU4159040 4LBSWH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159040 4LBSWH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1433.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839784

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P839784

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92066
5°	91641
10°	89757
15°	86487
20°	82509
25°	78065
30°	73639
35°	69334
40°	65288
45°	60861
50°	55484
55°	49006
60°	41475
65°	32558
70°	23240
75°	12721
80°	2264
85°	0



TEST NUMBER: P839784

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	4.9
10°-20°	190.8	13.3
20°-30°	265.0	18.5
30°-40°	289.2	20.2
40°-50°	269.8	18.8
50°-60°	204.7	14.3
60°-70°	112.1	7.8
70°-80°	30.8	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	526.0	36.7
0°-40°	815.1	56.9
0°-60°	1289.6	90.0
0°-90°	1433.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1433.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	749	
5°	743	70
15°	680	191
25°	576	265
35°	462	289
45°	350	270
55°	229	205
65°	112	112
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P839784

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	749.4
2.5°	749.4
5°	743.1
7.5°	733.7
10°	719.5
12.5°	700.6
15°	680.0
17.5°	654.8
20°	631.1
22.5°	602.7
25°	575.9
27.5°	549.1
30°	519.1
32.5°	490.7
35°	462.3
37.5°	433.9
40°	407.1
42.5°	378.7
45°	350.3
47.5°	321.9
50°	290.3
52.5°	260.3
55°	228.8
57.5°	198.8
60°	168.8
62.5°	138.9
65°	112.0
67.5°	86.8
70°	64.7
72.5°	44.2
75°	26.8
77.5°	12.6
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)