

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839785

Luminaire Tested: **LDS4C15D010 EU4159040 4LBSWMH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159040 4LBSWMH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1368.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839785

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839785

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87902
5°	87485
10°	85677
15°	82570
20°	78770
25°	74527
30°	70291
35°	66185
40°	62321
45°	58099
50°	52980
55°	46779
60°	39608
65°	31075
70°	22199
75°	12152
80°	2122
85°	0



TEST NUMBER: P839785

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.0	4.9
10°-20°	182.2	13.3
20°-30°	253.0	18.5
30°-40°	276.0	20.2
40°-50°	257.5	18.8
50°-60°	195.5	14.3
60°-70°	107.0	7.8
70°-80°	29.4	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.1	36.7
0°-40°	778.2	56.9
0°-60°	1231.1	90.0
0°-90°	1368.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1368.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	716	
5°	709	67
15°	649	182
25°	550	253
35°	441	276
45°	334	258
55°	218	195
65°	107	107
75°	26	29
85°	0	0
90°	0	



TEST NUMBER: P839785

CATALOG NUMBER: LDS4C15D010 EU4159040 4LBSWMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	715.5
2.5°	715.5
5°	709.4
7.5°	700.4
10°	686.8
12.5°	668.8
15°	649.2
17.5°	625.1
20°	602.5
22.5°	575.4
25°	549.8
27.5°	524.2
30°	495.5
32.5°	468.4
35°	441.3
37.5°	414.2
40°	388.6
42.5°	361.5
45°	334.4
47.5°	307.3
50°	277.2
52.5°	248.5
55°	218.4
57.5°	189.8
60°	161.2
62.5°	132.6
65°	106.9
67.5°	82.8
70°	61.8
72.5°	42.2
75°	25.6
77.5°	12.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)