

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839791

Luminaire Tested: **LDS4C15D010 EU4159050 4LBSGPH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C15D010 EU4159050 4LBSGPH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH GPH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1041.0 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839791

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBSGPH

Luminous Intensity Polar Plot





TEST NUMBER: P839791

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBSGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67152
5°	66927
10°	66192
15°	65044
20°	63591
25°	61894
30°	59935
35°	57636
40°	54720
45°	49759
50°	41073
55°	30243
60°	20541
65°	12035
70°	4741
75°	1092
80°	1415
85°	2396



TEST NUMBER: P839791

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBSGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	4.9
10°-20°	144.0	13.8
20°-30°	210.1	20.2
30°-40°	239.8	23.0
40°-50°	218.0	20.9
50°-60°	128.6	12.3
60°-70°	43.1	4.1
70°-80°	4.5	0.4
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.5	39.0
0°-40°	645.3	62.0
0°-60°	991.8	95.3
0°-90°	1041.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1041.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	547	
5°	543	51
15°	511	144
25°	457	210
35°	384	240
45°	286	218
55°	141	129
65°	41	43
75°	2	5
85°	2	2
90°	0	



TEST NUMBER: P839791

CATALOG NUMBER: LDS4C15D010 EU4159050 4LBSGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	546.6
2.5°	545.8
5°	542.7
7.5°	537.6
10°	530.6
12.5°	521.6
15°	511.4
17.5°	499.6
20°	486.4
22.5°	472.1
25°	456.6
27.5°	439.7
30°	422.5
32.5°	403.7
35°	384.3
37.5°	363.2
40°	341.2
42.5°	315.6
45°	286.4
47.5°	252.6
50°	214.9
52.5°	177.2
55°	141.2
57.5°	110.6
60°	83.6
62.5°	60.5
65°	41.4
67.5°	25.3
70°	13.2
72.5°	5.1
75°	2.3
77.5°	2.3
80°	2.0
82.5°	1.7
85°	1.7
87.5°	1.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)