

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839829

Luminaire Tested: **LDS4C20D010 EU4209040 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C20D010 EU4209040 4LBPSMMS
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1624.0 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839829

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839829

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90				90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79				79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70				70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62				62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55				55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49				49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44				44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40				40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33				33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104757
5°	104405
10°	103254
15°	101483
20°	99204
25°	96555
30°	93513
35°	89911
40°	85383
45°	77628
50°	64085
55°	47186
60°	32016
65°	18750
70°	7400
75°	1661
80°	2193
85°	3665



TEST NUMBER: P839829

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.2	4.9
10°-20°	224.7	13.8
20°-30°	327.7	20.2
30°-40°	374.1	23.0
40°-50°	340.1	20.9
50°-60°	200.6	12.3
60°-70°	67.3	4.1
70°-80°	7.0	0.4
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	632.6	39.0
0°-40°	1006.7	62.0
0°-60°	1547.3	95.3
0°-90°	1624.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1624.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	847	80
15°	798	225
25°	712	328
35°	600	374
45°	447	340
55°	220	201
65°	64	67
75°	4	7
85°	3	2
90°	0	



TEST NUMBER: P839829

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	852.7
2.5°	851.4
5°	846.6
7.5°	838.7
10°	827.7
12.5°	813.7
15°	797.9
17.5°	779.4
20°	758.8
22.5°	736.4
25°	712.3
27.5°	686.0
30°	659.2
32.5°	629.8
35°	599.5
37.5°	566.6
40°	532.4
42.5°	492.4
45°	446.8
47.5°	394.1
50°	335.3
52.5°	276.5
55°	220.3
57.5°	172.5
60°	130.3
62.5°	94.4
65°	64.5
67.5°	39.5
70°	20.6
72.5°	7.9
75°	3.5
77.5°	3.5
80°	3.1
82.5°	2.6
85°	2.6
87.5°	2.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)