

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839528

Luminaire Tested: **LD6C70D010 EU6709035 6LCSQWLI**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C70D010 EU6709035 6LCSQWLI
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LCSQW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7168.1 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839528

CATALOG NUMBER: LD6C70D010 EU6709035 6LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P839528

CATALOG NUMBER: LD6C70D010 EU6709035 6LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144740
5°	144506
10°	143716
15°	142054
20°	139477
25°	136458
30°	133205
35°	129406
40°	124197
45°	115210
50°	99255
55°	79171
60°	61638
65°	46141
70°	33486
75°	26550
80°	24869
85°	24799



TEST NUMBER: P839528

CATALOG NUMBER: LD6C70D010 EU6709035 6LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	317.4	4.4
10°-20°	897.5	12.5
20°-30°	1322.6	18.5
30°-40°	1536.5	21.4
40°-50°	1444.2	20.1
50°-60°	956.0	13.3
60°-70°	460.7	6.4
70°-80°	177.7	2.5
80°-90°	55.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2537.6	35.4
0°-40°	4074.0	56.8
0°-60°	6474.3	90.3
0°-90°	7168.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7168.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3362	
5°	3344	317
15°	3187	898
25°	2872	1323
35°	2462	1536
45°	1892	1444
55°	1055	956
65°	453	461
75°	160	178
85°	50	55
90°	0	



TEST NUMBER: P839528

CATALOG NUMBER: LD6C70D010 EU6709035 6LCSQWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3361.7
2.5°	3358.7
5°	3343.5
7.5°	3320.7
10°	3287.2
12.5°	3241.7
15°	3186.9
17.5°	3120.1
20°	3044.1
22.5°	2960.5
25°	2872.4
27.5°	2778.1
30°	2679.3
32.5°	2574.5
35°	2462.0
37.5°	2338.9
40°	2209.7
42.5°	2063.8
45°	1892.1
47.5°	1697.6
50°	1481.8
52.5°	1262.9
55°	1054.7
57.5°	875.4
60°	715.8
62.5°	573.0
65°	452.9
67.5°	351.1
70°	266.0
72.5°	202.1
75°	159.6
77.5°	129.2
80°	100.3
82.5°	74.5
85°	50.2
87.5°	28.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)