

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839832

Luminaire Tested: **LDS4C20D010 EU4209040 4LBSH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C20D010 EU4209040 4LBSH
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1987.0 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839832

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839832

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127669
5°	127072
10°	124449
15°	119925
20°	114409
25°	108240
30°	102110
35°	96135
40°	90515
45°	84386
50°	76947
55°	67941
60°	57520
65°	45145
70°	32220
75°	17658
80°	3113
85°	0



TEST NUMBER: P839832

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.3	4.9
10°-20°	264.6	13.3
20°-30°	367.4	18.5
30°-40°	400.9	20.2
40°-50°	374.0	18.8
50°-60°	283.9	14.3
60°-70°	155.4	7.8
70°-80°	42.8	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.3	36.7
0°-40°	1130.3	56.9
0°-60°	1788.2	90.0
0°-90°	1987.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1987.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1039	
5°	1030	97
15°	943	265
25°	798	367
35°	641	401
45°	486	374
55°	317	284
65°	155	155
75°	37	43
85°	0	1
90°	0	



TEST NUMBER: P839832

CATALOG NUMBER: LDS4C20D010 EU4209040 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1039.2
2.5°	1039.2
5°	1030.4
7.5°	1017.3
10°	997.6
12.5°	971.4
15°	942.9
17.5°	908.0
20°	875.1
22.5°	835.7
25°	798.5
27.5°	761.4
30°	719.8
32.5°	680.4
35°	641.0
37.5°	601.6
40°	564.4
42.5°	525.1
45°	485.7
47.5°	446.3
50°	402.6
52.5°	361.0
55°	317.2
57.5°	275.6
60°	234.1
62.5°	192.5
65°	155.3
67.5°	120.3
70°	89.7
72.5°	61.3
75°	37.2
77.5°	17.5
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)