

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839532

Luminaire Tested: **LD6C75D010 EU6759030 6LCSQWLI**

Issue Date: 6/29/2023



Test Information

Test Method: LM-79-08
Report Number: P839532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C75D010 EU6759030 6LCSQWLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LCSQW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8311.0 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839532

CATALOG NUMBER: LD6C75D010 EU6759030 6LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P839532

CATALOG NUMBER: LD6C75D010 EU6759030 6LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167822
5°	167547
10°	166634
15°	164707
20°	161718
25°	158216
30°	154449
35°	150041
40°	144003
45°	133580
50°	115076
55°	91797
60°	71464
65°	53496
70°	38823
75°	30776
80°	28836
85°	28702



TEST NUMBER: P839532

CATALOG NUMBER: LD6C75D010 EU6759030 6LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.0	4.4
10°-20°	1040.6	12.5
20°-30°	1533.5	18.5
30°-40°	1781.5	21.4
40°-50°	1674.5	20.1
50°-60°	1108.4	13.3
60°-70°	534.1	6.4
70°-80°	206.0	2.5
80°-90°	64.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2942.2	35.4
0°-40°	4723.7	56.8
0°-60°	7506.6	90.3
0°-90°	8311.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8311.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3898	
5°	3877	368
15°	3695	1041
25°	3330	1534
35°	2855	1781
45°	2194	1675
55°	1223	1108
65°	525	534
75°	185	206
85°	58	64
90°	0	



TEST NUMBER: P839532

CATALOG NUMBER: LD6C75D010 EU6759030 6LCSQWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3897.8
2.5°	3894.2
5°	3876.6
7.5°	3850.2
10°	3811.4
12.5°	3758.6
15°	3695.1
17.5°	3617.6
20°	3529.5
22.5°	3432.6
25°	3330.4
27.5°	3221.1
30°	3106.6
32.5°	2985.0
35°	2854.6
37.5°	2711.9
40°	2562.1
42.5°	2392.9
45°	2193.8
47.5°	1968.3
50°	1718.0
52.5°	1464.3
55°	1222.9
57.5°	1015.0
60°	829.9
62.5°	664.3
65°	525.1
67.5°	407.0
70°	308.4
72.5°	234.4
75°	185.0
77.5°	149.8
80°	116.3
82.5°	86.3
85°	58.1
87.5°	33.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)