

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839540

Luminaire Tested: **LD6C80D010 EU6809050 6LCSQWLI**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C80D010 EU6809050 6LCSQWLI
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LCSQW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9305.0 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839540

CATALOG NUMBER: LD6C80D010 EU6809050 6LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P839540

CATALOG NUMBER: LD6C80D010 EU6809050 6LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187891
5°	187588
10°	186566
15°	184409
20°	181058
25°	177138
30°	172919
35°	167986
40°	161225
45°	149558
50°	128841
55°	102779
60°	80015
65°	59894
70°	43456
75°	34452
80°	32283
85°	32160



TEST NUMBER: P839540

CATALOG NUMBER: LD6C80D010 EU6809050 6LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	412.0	4.4
10°-20°	1165.1	12.5
20°-30°	1717.0	18.5
30°-40°	1994.5	21.4
40°-50°	1874.8	20.1
50°-60°	1241.0	13.3
60°-70°	598.0	6.4
70°-80°	230.6	2.5
80°-90°	72.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3294.1	35.4
0°-40°	5288.6	56.8
0°-60°	8404.4	90.3
0°-90°	9305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9305.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4364	
5°	4340	412
15°	4137	1165
25°	3729	1717
35°	3196	1995
45°	2456	1875
55°	1369	1241
65°	588	598
75°	207	231
85°	65	72
90°	0	



TEST NUMBER: P839540

CATALOG NUMBER: LD6C80D010 EU6809050 6LCSQWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4363.9
2.5°	4360.0
5°	4340.3
7.5°	4310.7
10°	4267.3
12.5°	4208.1
15°	4137.1
17.5°	4050.3
20°	3951.6
22.5°	3843.1
25°	3728.7
27.5°	3606.4
30°	3478.1
32.5°	3342.0
35°	3196.0
37.5°	3036.2
40°	2868.5
42.5°	2679.1
45°	2456.2
47.5°	2203.7
50°	1923.5
52.5°	1639.4
55°	1369.2
57.5°	1136.4
60°	929.2
62.5°	743.8
65°	587.9
67.5°	455.7
70°	345.2
72.5°	262.4
75°	207.1
77.5°	167.7
80°	130.2
82.5°	96.7
85°	65.1
87.5°	37.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)