

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839849

Luminaire Tested: **LDS4C25D010 EU4259027 4LBPSMMS**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839849  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C25D010 EU4259027 4LBPSMMS  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBPS TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1932.0 lumens  
Efficiency: N/A  
Efficacy: 61.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839849

CATALOG NUMBER: LDS4C25D010 EU4259027 4LBPSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P839849

CATALOG NUMBER: LDS4C25D010 EU4259027 4LBPSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	124635
5°	124198
10°	122840
15°	120726
20°	118017
25°	114868
30°	111246
35°	106963
40°	101565
45°	92343
50°	76240
55°	56139
60°	38109
65°	22325
70°	8800
75°	1994
80°	2618
85°	4370



TEST NUMBER: P839849

CATALOG NUMBER: LDS4C25D010 EU4259027 4LBPSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.4	4.9
10°-20°	267.3	13.8
20°-30°	389.9	20.2
30°-40°	445.0	23.0
40°-50°	404.6	20.9
50°-60°	238.6	12.3
60°-70°	80.0	4.1
70°-80°	8.4	0.4
80°-90°	2.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	752.6	39.0
0°-40°	1197.6	62.0
0°-60°	1840.7	95.3
0°-90°	1932.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1932.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1014	
5°	1007	95
15°	949	267
25°	847	390
35°	713	445
45°	532	405
55°	262	239
65°	77	80
75°	4	8
85°	3	3
90°	0	



TEST NUMBER: P839849

CATALOG NUMBER: LDS4C25D010 EU4259027 4LBPSMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1014.5
2.5°	1012.9
5°	1007.1
7.5°	997.8
10°	984.7
12.5°	968.0
15°	949.2
17.5°	927.3
20°	902.7
22.5°	876.1
25°	847.4
27.5°	816.1
30°	784.2
32.5°	749.2
35°	713.2
37.5°	674.0
40°	633.3
42.5°	585.8
45°	531.5
47.5°	468.9
50°	398.9
52.5°	328.9
55°	262.1
57.5°	205.2
60°	155.1
62.5°	112.3
65°	76.8
67.5°	47.0
70°	24.5
72.5°	9.4
75°	4.2
77.5°	4.2
80°	3.7
82.5°	3.1
85°	3.1
87.5°	2.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)