

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839544

Luminaire Tested: **LD6C90D010 EU6909040 6LCSQWLI**

Issue Date: 6/29/2023



Test Information

Test Method: LM-79-08
Report Number: P839544
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C90D010 EU6909040 6LCSQWLI
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LCSQW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9710.0 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839544

CATALOG NUMBER: LD6C90D010 EU6909040 6LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P839544

CATALOG NUMBER: LD6C90D010 EU6909040 6LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196071
5°	195753
10°	194685
15°	192433
20°	188939
25°	184848
30°	180446
35°	175297
40°	168245
45°	156067
50°	134448
55°	107253
60°	83502
65°	62502
70°	45357
75°	35966
80°	33696
85°	33543



TEST NUMBER: P839544

CATALOG NUMBER: LD6C90D010 EU6909040 6LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.0	4.4
10°-20°	1215.8	12.5
20°-30°	1791.7	18.5
30°-40°	2081.4	21.4
40°-50°	1956.4	20.1
50°-60°	1295.0	13.3
60°-70°	624.0	6.4
70°-80°	240.7	2.5
80°-90°	75.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3437.4	35.4
0°-40°	5518.8	56.8
0°-60°	8770.2	90.3
0°-90°	9710.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9710.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4554	
5°	4529	430
15°	4317	1216
25°	3891	1792
35°	3335	2081
45°	2563	1956
55°	1429	1295
65°	614	624
75°	216	241
85°	68	75
90°	0	



TEST NUMBER: P839544

CATALOG NUMBER: LD6C90D010 EU6909040 6LCSQWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4553.9
2.5°	4549.8
5°	4529.2
7.5°	4498.3
10°	4453.0
12.5°	4391.2
15°	4317.1
17.5°	4226.5
20°	4123.6
22.5°	4010.4
25°	3891.0
27.5°	3763.3
30°	3629.5
32.5°	3487.5
35°	3335.1
37.5°	3168.4
40°	2993.4
42.5°	2795.7
45°	2563.1
47.5°	2299.6
50°	2007.2
52.5°	1710.8
55°	1428.8
57.5°	1185.8
60°	969.7
62.5°	776.1
65°	613.5
67.5°	475.6
70°	360.3
72.5°	273.8
75°	216.2
77.5°	175.0
80°	135.9
82.5°	100.9
85°	67.9
87.5°	39.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)