

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839561

Luminaire Tested: **LDS4C05D010 EU4059030 4LBSGPH**

Issue Date: 8/24/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P839561  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C05D010 EU4059030 4LBSGPH  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBS TRIM WITH GPH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 425.0 lumens  
Efficiency: N/A  
Efficacy: 59.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839561

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBSGPH

### Luminous Intensity Polar Plot





TEST NUMBER: P839561

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBSGPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27421
5°	27328
10°	27021
15°	26557
20°	25965
25°	25267
30°	24471
35°	23531
40°	22340
45°	20310
50°	16762
55°	12359
60°	8379
65°	4913
70°	1940
75°	427
80°	566
85°	987



TEST NUMBER: P839561

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBSGPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.0	4.9
10°-20°	58.8	13.8
20°-30°	85.8	20.2
30°-40°	97.9	23.0
40°-50°	89.0	20.9
50°-60°	52.5	12.4
60°-70°	17.6	4.1
70°-80°	1.8	0.4
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.5	39.0
0°-40°	263.4	62.0
0°-60°	404.9	95.3
0°-90°	425.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	425.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	223	
5°	222	21
15°	209	59
25°	186	86
35°	157	98
45°	117	89
55°	58	52
65°	17	18
75°	1	2
85°	1	1
90°	0	



TEST NUMBER: P839561

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBSGPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	223.2
2.5°	222.8
5°	221.6
7.5°	219.5
10°	216.6
12.5°	212.9
15°	208.8
17.5°	204.0
20°	198.6
22.5°	192.7
25°	186.4
27.5°	179.5
30°	172.5
32.5°	164.8
35°	156.9
37.5°	148.3
40°	139.3
42.5°	128.9
45°	116.9
47.5°	103.1
50°	87.7
52.5°	72.4
55°	57.7
57.5°	45.1
60°	34.1
62.5°	24.7
65°	16.9
67.5°	10.3
70°	5.4
72.5°	2.1
75°	0.9
77.5°	0.9
80°	0.8
82.5°	0.7
85°	0.7
87.5°	0.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)