

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839568

Luminaire Tested: **LDS4C05D010 EU4059035 4LBPSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C05D010 EU4059035 4LBPSMB
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 521.0 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839568

CATALOG NUMBER: LDS4C05D010 EU4059035 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839568

CATALOG NUMBER: LDS4C05D010 EU4059035 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33613
5°	33494
10°	33121
15°	32560
20°	31822
25°	30974
30°	30003
35°	28840
40°	27392
45°	24897
50°	20565
55°	15143
60°	10271
65°	6017
70°	2371
75°	522
80°	707
85°	1128



TEST NUMBER: P839568

CATALOG NUMBER: LDS4C05D010 EU4059035 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.7	4.9
10°-20°	72.1	13.8
20°-30°	105.1	20.2
30°-40°	120.0	23.0
40°-50°	109.1	20.9
50°-60°	64.3	12.4
60°-70°	21.6	4.1
70°-80°	2.2	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.9	39.0
0°-40°	322.9	62.0
0°-60°	496.4	95.3
0°-90°	521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	521.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	272	26
15°	256	72
25°	228	105
35°	192	120
45°	143	109
55°	71	64
65°	21	22
75°	1	2
85°	1	1
90°	0	



TEST NUMBER: P839568

CATALOG NUMBER: LDS4C05D010 EU4059035 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	273.6
2.5°	273.1
5°	271.6
7.5°	269.1
10°	265.5
12.5°	261.0
15°	256.0
17.5°	250.1
20°	243.4
22.5°	236.3
25°	228.5
27.5°	220.1
30°	211.5
32.5°	202.0
35°	192.3
37.5°	181.8
40°	170.8
42.5°	158.0
45°	143.3
47.5°	126.4
50°	107.6
52.5°	88.7
55°	70.7
57.5°	55.3
60°	41.8
62.5°	30.3
65°	20.7
67.5°	12.7
70°	6.6
72.5°	2.5
75°	1.1
77.5°	1.1
80°	1.0
82.5°	0.8
85°	0.8
87.5°	0.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)