

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839861

Luminaire Tested: **LDS4C25D010 EU4259030 4LBSGPH**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C25D010 EU4259030 4LBSGPH
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH GPH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1628.0 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839861

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSGPH

Luminous Intensity Polar Plot





TEST NUMBER: P839861

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105015
5°	104664
10°	103516
15°	101724
20°	99452
25°	96785
30°	93740
35°	90136
40°	85592
45°	77819
50°	64237
55°	47314
60°	32114
65°	18808
70°	7435
75°	1661
80°	2193
85°	3665



TEST NUMBER: P839861

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	4.9
10°-20°	225.2	13.8
20°-30°	328.5	20.2
30°-40°	375.0	23.0
40°-50°	340.9	20.9
50°-60°	201.1	12.4
60°-70°	67.4	4.1
70°-80°	7.0	0.4
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	634.1	39.0
0°-40°	1009.1	62.0
0°-60°	1551.1	95.3
0°-90°	1628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1628.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	855	
5°	849	80
15°	800	225
25°	714	328
35°	601	375
45°	448	341
55°	221	201
65°	65	67
75°	4	7
85°	3	2
90°	0	



TEST NUMBER: P839861

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	854.8
2.5°	853.5
5°	848.7
7.5°	840.8
10°	829.8
12.5°	815.7
15°	799.8
17.5°	781.4
20°	760.7
22.5°	738.2
25°	714.0
27.5°	687.6
30°	660.8
32.5°	631.3
35°	601.0
37.5°	568.0
40°	533.7
42.5°	493.6
45°	447.9
47.5°	395.1
50°	336.1
52.5°	277.2
55°	220.9
57.5°	172.9
60°	130.7
62.5°	94.6
65°	64.7
67.5°	39.6
70°	20.7
72.5°	7.9
75°	3.5
77.5°	3.5
80°	3.1
82.5°	2.6
85°	2.6
87.5°	2.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)