

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839598

Luminaire Tested: **LDS4C08D010 EU4089027 4LBPSMB**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839598  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C08D010 EU4089027 4LBPSMB  
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 4LBPS TRIM WITH MB FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 664.0 lumens  
Efficiency: N/A  
Efficacy: 67.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839598

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMB

### Luminous Intensity Polar Plot





TEST NUMBER: P839598

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	42839
5°	42682
10°	42215
15°	41488
20°	40568
25°	39473
30°	38231
35°	36759
40°	34913
45°	31742
50°	26203
55°	19298
60°	13096
65°	7674
70°	3017
75°	665
80°	920
85°	1551



TEST NUMBER: P839598

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.8	4.9
10°-20°	91.9	13.8
20°-30°	134.0	20.2
30°-40°	152.9	23.0
40°-50°	139.0	20.9
50°-60°	82.0	12.3
60°-70°	27.5	4.1
70°-80°	2.8	0.4
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.6	39.0
0°-40°	411.6	62.0
0°-60°	632.6	95.3
0°-90°	664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	349	
5°	346	33
15°	326	92
25°	291	134
35°	245	153
45°	183	139
55°	90	82
65°	26	27
75°	1	3
85°	1	1
90°	0	



TEST NUMBER: P839598

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	348.7
2.5°	348.1
5°	346.1
7.5°	342.9
10°	338.4
12.5°	332.7
15°	326.2
17.5°	318.7
20°	310.3
22.5°	301.1
25°	291.2
27.5°	280.5
30°	269.5
32.5°	257.5
35°	245.1
37.5°	231.7
40°	217.7
42.5°	201.3
45°	182.7
47.5°	161.1
50°	137.1
52.5°	113.0
55°	90.1
57.5°	70.5
60°	53.3
62.5°	38.6
65°	26.4
67.5°	16.1
70°	8.4
72.5°	3.2
75°	1.4
77.5°	1.4
80°	1.3
82.5°	1.1
85°	1.1
87.5°	0.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)