

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839864

Luminaire Tested: **LDS4C25D010 EU4259030 4LBSWH**

Issue Date: 8/24/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P839864  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C25D010 EU4259030 4LBSWH  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBS TRIM WITH WH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2286.0 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839864

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWH

### Luminous Intensity Polar Plot





TEST NUMBER: P839864

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146884
5°	146199
10°	143187
15°	137973
20°	131627
25°	124533
30°	117473
35°	110608
40°	104147
45°	97086
50°	88530
55°	78179
60°	66169
65°	51947
70°	37069
75°	20316
80°	3608
85°	0



TEST NUMBER: P839864

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.0	4.9
10°-20°	304.4	13.3
20°-30°	422.7	18.5
30°-40°	461.3	20.2
40°-50°	430.3	18.8
50°-60°	326.6	14.3
60°-70°	178.8	7.8
70°-80°	49.2	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	839.1	36.7
0°-40°	1300.4	56.9
0°-60°	2057.3	90.0
0°-90°	2286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2286.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1196	
5°	1186	112
15°	1085	304
25°	919	423
35°	738	461
45°	559	430
55°	365	327
65°	179	179
75°	43	49
85°	0	1
90°	0	



TEST NUMBER: P839864

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1195.6
2.5°	1195.6
5°	1185.5
7.5°	1170.4
10°	1147.8
12.5°	1117.6
15°	1084.8
17.5°	1044.6
20°	1006.8
22.5°	961.5
25°	918.7
27.5°	875.9
30°	828.1
32.5°	782.8
35°	737.5
37.5°	692.2
40°	649.4
42.5°	604.1
45°	558.8
47.5°	513.5
50°	463.2
52.5°	415.3
55°	365.0
57.5°	317.1
60°	269.3
62.5°	221.5
65°	178.7
67.5°	138.4
70°	103.2
72.5°	70.5
75°	42.8
77.5°	20.1
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)