

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839865

Luminaire Tested: **LDS4C25D010 EU4259030 4LBSWMH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C25D010 EU4259030 4LBSWMH
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2182.0 lumens
Efficiency: N/A
Efficacy: 69.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839865

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839865

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140200
5°	139552
10°	136662
15°	131702
20°	125639
25°	118867
30°	112125
35°	105568
40°	99400
45°	92656
50°	84497
55°	74623
60°	63171
65°	49593
70°	35381
75°	19414
80°	3396
85°	0



TEST NUMBER: P839865

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.9	4.9
10°-20°	290.5	13.3
20°-30°	403.5	18.5
30°-40°	440.3	20.2
40°-50°	410.7	18.8
50°-60°	311.8	14.3
60°-70°	170.7	7.8
70°-80°	47.0	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.9	36.7
0°-40°	1241.2	56.9
0°-60°	1963.7	90.0
0°-90°	2182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2182.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1141	
5°	1132	107
15°	1036	291
25°	877	403
35°	704	440
45°	533	411
55°	348	312
65°	171	171
75°	41	47
85°	0	1
90°	0	



TEST NUMBER: P839865

CATALOG NUMBER: LDS4C25D010 EU4259030 4LBSWMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1141.2
2.5°	1141.2
5°	1131.6
7.5°	1117.2
10°	1095.5
12.5°	1066.7
15°	1035.5
17.5°	997.1
20°	961.0
22.5°	917.7
25°	876.9
27.5°	836.1
30°	790.4
32.5°	747.2
35°	703.9
37.5°	660.7
40°	619.8
42.5°	576.6
45°	533.3
47.5°	490.1
50°	442.1
52.5°	396.4
55°	348.4
57.5°	302.7
60°	257.1
62.5°	211.4
65°	170.6
67.5°	132.1
70°	98.5
72.5°	67.3
75°	40.9
77.5°	19.2
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)