

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839599

Luminaire Tested: **LDS4C08D010 EU4089027 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089027 4LBPSMMS
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 679.0 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839599

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839599

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43797
5°	43656
10°	43176
15°	42430
20°	41483
25°	40368
30°	39096
35°	37599
40°	35699
45°	32455
50°	26796
55°	19727
60°	13391
65°	7849
70°	3089
75°	712
80°	920
85°	1551



TEST NUMBER: P839599

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.5	4.9
10°-20°	93.9	13.8
20°-30°	137.0	20.2
30°-40°	156.4	23.0
40°-50°	142.2	20.9
50°-60°	83.9	12.3
60°-70°	28.1	4.1
70°-80°	3.0	0.4
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	264.5	39.0
0°-40°	420.9	62.0
0°-60°	646.9	95.3
0°-90°	679.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	679.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	356	
5°	354	34
15°	334	94
25°	298	137
35°	251	156
45°	187	142
55°	92	84
65°	27	28
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839599

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	356.5
2.5°	356.0
5°	354.0
7.5°	350.7
10°	346.1
12.5°	340.2
15°	333.6
17.5°	325.9
20°	317.3
22.5°	307.9
25°	297.8
27.5°	286.8
30°	275.6
32.5°	263.3
35°	250.7
37.5°	236.9
40°	222.6
42.5°	205.9
45°	186.8
47.5°	164.8
50°	140.2
52.5°	115.6
55°	92.1
57.5°	72.1
60°	54.5
62.5°	39.5
65°	27.0
67.5°	16.5
70°	8.6
72.5°	3.3
75°	1.5
77.5°	1.5
80°	1.3
82.5°	1.1
85°	1.1
87.5°	0.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)