

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839875

Luminaire Tested: **LDS4C25D010 EU4259035 4LBSWMH**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839875  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C25D010 EU4259035 4LBSWMH  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBS TRIM WITH WMH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2213.0 lumens  
Efficiency: N/A  
Efficacy: 70.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839875

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBSWMH

### Luminous Intensity Polar Plot





TEST NUMBER: P839875

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBSWMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	142191
5°	141525
10°	138608
15°	133572
20°	127417
25°	120548
30°	113714
35°	107068
40°	100811
45°	93977
50°	85701
55°	75673
60°	64056
65°	50290
70°	35884
75°	19651
80°	3467
85°	0



TEST NUMBER: P839875

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBSWMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.4	4.9
10°-20°	294.7	13.3
20°-30°	409.2	18.5
30°-40°	446.5	20.2
40°-50°	416.6	18.8
50°-60°	316.2	14.3
60°-70°	173.1	7.8
70°-80°	47.6	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	812.3	36.7
0°-40°	1258.8	56.9
0°-60°	1991.6	90.0
0°-90°	2213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2213.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1157	
5°	1148	108
15°	1050	295
25°	889	409
35°	714	447
45°	541	417
55°	353	316
65°	173	173
75°	41	48
85°	0	1
90°	0	



TEST NUMBER: P839875

CATALOG NUMBER: LDS4C25D010 EU4259035 4LBSWMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1157.4
2.5°	1157.4
5°	1147.6
7.5°	1133.1
10°	1111.1
12.5°	1081.9
15°	1050.2
17.5°	1011.2
20°	974.6
22.5°	930.8
25°	889.3
27.5°	848.0
30°	801.6
32.5°	757.8
35°	713.9
37.5°	670.1
40°	628.6
42.5°	584.8
45°	540.9
47.5°	497.1
50°	448.4
52.5°	402.0
55°	353.3
57.5°	307.0
60°	260.7
62.5°	214.4
65°	173.0
67.5°	134.0
70°	99.9
72.5°	68.2
75°	41.4
77.5°	19.5
80°	4.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)