

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839877

Luminaire Tested: **LDS4C25D010 EU4259040 4LBCSMMS**

Issue Date: 8/24/2022

Test Information

Test Method: LM-79-08
Report Number: P839877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C25D010 EU4259040 4LBCSMMS
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBCS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1796.0 lumens
Efficiency: N/A
Efficacy: 57.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839877

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839877

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115851
5°	115467
10°	114195
15°	112230
20°	109715
25°	106776
30°	103415
35°	99434
40°	94412
45°	85845
50°	70870
55°	52176
60°	35431
65°	20727
70°	8190
75°	1851
80°	2405
85°	4088



TEST NUMBER: P839877

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	4.9
10°-20°	248.5	13.8
20°-30°	362.4	20.2
30°-40°	413.7	23.0
40°-50°	376.1	20.9
50°-60°	221.8	12.3
60°-70°	74.4	4.1
70°-80°	7.8	0.4
80°-90°	2.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.6	39.0
0°-40°	1113.2	62.0
0°-60°	1711.1	95.3
0°-90°	1796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	943	
5°	936	89
15°	882	248
25°	788	362
35°	663	414
45°	494	376
55°	244	222
65°	71	74
75°	4	8
85°	3	3
90°	0	



TEST NUMBER: P839877

CATALOG NUMBER: LDS4C25D010 EU4259040 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	943.0
2.5°	941.6
5°	936.3
7.5°	927.5
10°	915.4
12.5°	899.8
15°	882.4
17.5°	862.0
20°	839.2
22.5°	814.4
25°	787.7
27.5°	758.6
30°	729.0
32.5°	696.5
35°	663.0
37.5°	626.6
40°	588.7
42.5°	544.6
45°	494.1
47.5°	435.8
50°	370.8
52.5°	305.8
55°	243.6
57.5°	190.7
60°	144.2
62.5°	104.4
65°	71.3
67.5°	43.7
70°	22.8
72.5°	8.7
75°	3.9
77.5°	3.9
80°	3.4
82.5°	2.9
85°	2.9
87.5°	2.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)