

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839609

Luminaire Tested: **LDS4C08D010 EU4089030 4LBPSMMS**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839609  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C08D010 EU4089030 4LBPSMMS  
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBPS TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 706.0 lumens  
Efficiency: N/A  
Efficacy: 71.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839609

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P839609

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	45542
5°	45383
10°	44885
15°	44121
20°	43130
25°	41981
30°	40657
35°	39084
40°	37111
45°	33741
50°	27866
55°	20519
60°	13932
65°	8139
70°	3233
75°	712
80°	920
85°	1551



TEST NUMBER: P839609

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.9	4.9
10°-20°	97.7	13.8
20°-30°	142.5	20.2
30°-40°	162.6	23.0
40°-50°	147.8	20.9
50°-60°	87.2	12.4
60°-70°	29.2	4.1
70°-80°	3.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	275.0	39.0
0°-40°	437.6	62.0
0°-60°	672.6	95.3
0°-90°	706.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	371	
5°	368	35
15°	347	98
25°	310	142
35°	261	163
45°	194	148
55°	96	87
65°	28	29
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839609

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	370.7
2.5°	370.1
5°	368.0
7.5°	364.6
10°	359.8
12.5°	353.7
15°	346.9
17.5°	338.8
20°	329.9
22.5°	320.1
25°	309.7
27.5°	298.2
30°	286.6
32.5°	273.8
35°	260.6
37.5°	246.3
40°	231.4
42.5°	214.1
45°	194.2
47.5°	171.3
50°	145.8
52.5°	120.2
55°	95.8
57.5°	75.0
60°	56.7
62.5°	41.0
65°	28.0
67.5°	17.2
70°	9.0
72.5°	3.4
75°	1.5
77.5°	1.5
80°	1.3
82.5°	1.1
85°	1.1
87.5°	1.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)