

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839890

Luminaire Tested: **LDS4C25D010 EU4259050 4LBSB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C25D010 EU4259050 4LBSB
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH B FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1400.0 lumens
Efficiency: N/A
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839890

CATALOG NUMBER: LDS4C25D010 EU4259050 4LBSB

Luminous Intensity Polar Plot





TEST NUMBER: P839890

CATALOG NUMBER: LDS4C25D010 EU4259050 4LBSB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70																			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62																			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55																			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90310
5°	90001
10°	89008
15°	87479
20°	85516
25°	83230
30°	80618
35°	77508
40°	73596
45°	66908
50°	55255
55°	40674
60°	27617
65°	16163
70°	6394
75°	1424
80°	1839
85°	3242



TEST NUMBER: P839890

CATALOG NUMBER: LDS4C25D010 EU4259050 4LBSB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	4.9
10°-20°	193.7	13.8
20°-30°	282.5	20.2
30°-40°	322.5	23.0
40°-50°	293.1	20.9
50°-60°	172.9	12.4
60°-70°	58.0	4.1
70°-80°	6.0	0.4
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.3	39.0
0°-40°	867.8	62.0
0°-60°	1333.8	95.3
0°-90°	1400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	735	
5°	730	69
15°	688	194
25°	614	282
35°	517	322
45°	385	293
55°	190	173
65°	56	58
75°	3	6
85°	2	2
90°	0	



TEST NUMBER: P839890

CATALOG NUMBER: LDS4C25D010 EU4259050 4LBSB

CANDELA DISTRIBUTION (FULL):

	0°
0°	735.1
2.5°	734.0
5°	729.8
7.5°	723.0
10°	713.5
12.5°	701.4
15°	687.8
17.5°	671.9
20°	654.1
22.5°	634.9
25°	614.0
27.5°	591.3
30°	568.3
32.5°	542.9
35°	516.8
37.5°	488.4
40°	458.9
42.5°	424.5
45°	385.1
47.5°	339.7
50°	289.1
52.5°	238.4
55°	189.9
57.5°	148.7
60°	112.4
62.5°	81.3
65°	55.6
67.5°	34.1
70°	17.8
72.5°	6.8
75°	3.0
77.5°	3.0
80°	2.6
82.5°	2.3
85°	2.3
87.5°	1.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)