

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839898

Luminaire Tested: **LDS4C30D010 EU4309027 4LBPSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309027 4LBPSMB
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2218.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839898

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839898

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143075
5°	142586
10°	141028
15°	138596
20°	135497
25°	131867
30°	127716
35°	122801
40°	116608
45°	106017
50°	87517
55°	64449
60°	43736
65°	25610
70°	10129
75°	2278
80°	2971
85°	5075



TEST NUMBER: P839898

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	4.9
10°-20°	306.8	13.8
20°-30°	447.6	20.2
30°-40°	510.9	23.0
40°-50°	464.4	20.9
50°-60°	273.9	12.3
60°-70°	91.9	4.1
70°-80°	9.6	0.4
80°-90°	3.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	864.0	39.0
0°-40°	1374.8	62.0
0°-60°	2113.2	95.3
0°-90°	2218.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2218.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1165	
5°	1156	110
15°	1090	307
25°	973	448
35°	819	511
45°	610	464
55°	301	274
65°	88	92
75°	5	10
85°	4	3
90°	0	



TEST NUMBER: P839898

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1164.6
2.5°	1162.8
5°	1156.2
7.5°	1145.5
10°	1130.5
12.5°	1111.3
15°	1089.7
17.5°	1064.5
20°	1036.4
22.5°	1005.8
25°	972.8
27.5°	936.9
30°	900.3
32.5°	860.1
35°	818.8
37.5°	773.8
40°	727.1
42.5°	672.5
45°	610.2
47.5°	538.3
50°	457.9
52.5°	377.6
55°	300.9
57.5°	235.6
60°	178.0
62.5°	128.9
65°	88.1
67.5°	53.9
70°	28.2
72.5°	10.8
75°	4.8
77.5°	4.8
80°	4.2
82.5°	3.6
85°	3.6
87.5°	3.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)