

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839899

Luminaire Tested: **LDS4C30D010 EU4309027 4LBPSMMS**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C30D010 EU4309027 4LBPSMMS
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBPS TRIM WITH MMS FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2268.0 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839899

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P839899

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146306
5°	145804
10°	144197
15°	141725
20°	138543
25°	134849
30°	130595
35°	125560
40°	119238
45°	108397
50°	89504
55°	65906
60°	44719
65°	26192
70°	10345
75°	2326
80°	3042
85°	5215



TEST NUMBER: P839899

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.0	4.9
10°-20°	313.8	13.8
20°-30°	457.7	20.2
30°-40°	522.4	23.0
40°-50°	474.9	20.9
50°-60°	280.1	12.3
60°-70°	93.9	4.1
70°-80°	9.8	0.4
80°-90°	3.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	883.4	39.0
0°-40°	1405.8	62.0
0°-60°	2160.8	95.3
0°-90°	2268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1191	
5°	1182	112
15°	1114	314
25°	995	458
35°	837	522
45°	624	475
55°	308	280
65°	90	94
75°	5	10
85°	4	3
90°	0	



TEST NUMBER: P839899

CATALOG NUMBER: LDS4C30D010 EU4309027 4LBPSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1190.9
2.5°	1189.0
5°	1182.3
7.5°	1171.3
10°	1155.9
12.5°	1136.3
15°	1114.3
17.5°	1088.5
20°	1059.7
22.5°	1028.5
25°	994.8
27.5°	958.0
30°	920.6
32.5°	879.5
35°	837.2
37.5°	791.3
40°	743.5
42.5°	687.7
45°	623.9
47.5°	550.4
50°	468.3
52.5°	386.1
55°	307.7
57.5°	240.9
60°	182.0
62.5°	131.8
65°	90.1
67.5°	55.2
70°	28.8
72.5°	11.0
75°	4.9
77.5°	4.9
80°	4.3
82.5°	3.7
85°	3.7
87.5°	3.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)