

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839615

Luminaire Tested: **LDS4C08D010 EU4089030 4LBSWMH**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839615  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C08D010 EU4089030 4LBSWMH  
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBS TRIM WITH WMH FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 767.0 lumens  
Efficiency: N/A  
Efficacy: 77.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839615

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWMH

### Luminous Intensity Polar Plot





TEST NUMBER: P839615

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49277
5°	49058
10°	48041
15°	46296
20°	44163
25°	41778
30°	39408
35°	37104
40°	34945
45°	32576
50°	29701
55°	26238
60°	22212
65°	17442
70°	12428
75°	6835
80°	1203
85°	0



TEST NUMBER: P839615

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.6	4.9
10°-20°	102.1	13.3
20°-30°	141.8	18.5
30°-40°	154.7	20.2
40°-50°	144.4	18.8
50°-60°	109.6	14.3
60°-70°	60.0	7.8
70°-80°	16.5	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.5	36.7
0°-40°	436.3	56.9
0°-60°	690.3	90.0
0°-90°	767.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	767.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	401	
5°	398	38
15°	364	102
25°	308	142
35°	247	155
45°	188	144
55°	122	110
65°	60	60
75°	14	17
85°	0	0
90°	0	



TEST NUMBER: P839615

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	401.1
2.5°	401.1
5°	397.8
7.5°	392.7
10°	385.1
12.5°	375.0
15°	364.0
17.5°	350.5
20°	337.8
22.5°	322.6
25°	308.2
27.5°	293.9
30°	277.8
32.5°	262.6
35°	247.4
37.5°	232.2
40°	217.9
42.5°	202.7
45°	187.5
47.5°	172.3
50°	155.4
52.5°	139.3
55°	122.5
57.5°	106.4
60°	90.4
62.5°	74.3
65°	60.0
67.5°	46.4
70°	34.6
72.5°	23.6
75°	14.4
77.5°	6.8
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)